

# PLR BP1

## Proloop Body Pack Induction Loop Receiver



Simple and convenient to use, this induction loop receiver is designed for use in induction-looped areas by listeners who do not wear T-coil-equipped hearing aids. Compatible with all IEC 60118-4 compliant induction loop systems.

### FEATURES

- Operates up to 200 hours with two AA alkaline batteries
- Simple to use -- on/off volume control
- Internal tone control
- 3.5mm stereo jack
- Compatible with 2-bay and 12-bay chargers (CHG 3502 and CHG 3512). Chargers sold separately.

# Proloop Body Pack Induction Loop Receiver

<b>Dimensions:</b>	4.1"H x 2.85"W x 1.38"D (104 mm H x 72 mm W x 35 mm D).
<b>Weight:</b>	4.6 oz (130 g) with batteries, 2.6 oz (73 g) without batteries.
<b>Color/Material:</b>	Black ABS/polycarbonate molded plastic case.
<b>Battery Type:</b>	(2) AA (1.5VDC) Alkaline or NiMH (rechargeable).
<b>Battery Life:</b>	Up to 200 hours with Alkaline batteries.
<b>LED Indicator:</b>	Green LED indicates power on, flashes when batteries are low.
<b>Headphone Jack:</b>	3.5mm stereo TRS jack works with mono or stereo headphones.
<b>Volume control:</b>	External switched thumb wheel controls power on/off and volume level.
<b>Tone control:</b>	Rotary control inside battery compartment (1kHz reference at 400mA/m input with Tone at mid position)
<b>Induction Coil:</b>	Maximum reception: receiver oriented vertically
<b>Power Output:</b>	35mW (max) into 33 ohms mono impedance
<b>THD:</b>	<2%
<b>Frequency Response:</b>	300Hz to 10KHz, -6dB

**NOTE: Specification subject to change without notice.**

## Architectural and Engineering Specifications

The receiver shall be a body pack style Induction loop receiver. It shall operate for up to 200 hrs with two AA Alkaline batteries and be housed in a black plastic enclosure. It shall have battery recharge ability utilizing drop-in chargers.

The receiver shall have a 3.5 mm headphone jack, on/off volume control. There shall be a tone control inside the battery compartment. It shall have a green power LED which will blink when the battery is low.

This receiver shall have a 2 year warranty.

This receiver shall be the model PLR BP1.

### Domestic Sales

Williams AV  
10300 Valley View Rd  
Eden Prairie, MN 55344  
Ph: 800-328-6190 / 952-943-2252  
FAX: 952-943-2174  
Email: [info@williamsav.com](mailto:info@williamsav.com)  
Web: [www.williamsav.com](http://www.williamsav.com)

### International Sales

International Sales Department  
Williams AV  
10300 Valley View Rd  
Eden Prairie, MN 55344 USA  
Phone: +1 952 943 2252  
Fax: +1 952 943 2174  
Email: [info@williamsav.com](mailto:info@williamsav.com)  
Web: [www.williamsav.com](http://www.williamsav.com)

**WILLIAMS AV**

[info@williamsav.com](mailto:info@williamsav.com) / [www.williamsav.com](http://www.williamsav.com)  
800-843-3544 / INTL: +1-952-943-2252